

SE-CURE™ 9650D

Flip Chip Attach Liquid Flux

Product Description

Kester SE-CURE™ 9650D is an ultra-low residue, no-clean liquid flux designed to be compatible with standard underfill materials. SE-CURE™ 9650D is an engineered product that eliminates the need to clean flip chip assemblies prior to underfill operations. This flux residue-to-underfill compatibility increases the overall adhesion of the polymer underfill system resulting in improved component integrity.

Performance Characteristics:

- Little to no residue after reflow
- Wide processing window
- Classified as ORL0 per J-STD-004
- Compliant to Bellcore GR-78

RoHS Compliance

This product meets the requirements of the Restriction of Hazardous Substances (RoHS) Directive, 2011/65/EU for the stated banned substances.

Physical Properties

Specific Gravity: 0.790

Anton-Paar DMA 35 @ 25 °C

Viscosity, Kinematic (typical): 2.74

1W-RD-G-17

Acid Number: 8

Tested to J-STD-004B, IPC-TM-650, Method 2.3.13

Quantitative Halides: None

Color: Clear, Colorless

Visual

Reliability Properties

Copper Mirror Corrosion: Low

Tested to J-STD-004, IPC-TM-650, Method 2.3.32

Copper Corrosion Test: Low

Tested to J-STD-004B, IPC-TM-650, Method 2.6.15

Chloride and Bromides: None detected

Tested to J-STD-004, IPC-TM-650, Method 2.3.33

Fluorides by Spot Test: Pass

Tested to J-STD-004, IPC-TM-650, Method 2.3.35.1

Surface Insulation Resistivity (SIR), IPC (typical): Pass

Tested to J-STD-004, IPC-TM-650, Method 2.6.3.3


	Blank	SE-CURE™ 9650D
Day 1	4.1*10 ¹⁰ Ω	4.5*10 ¹⁰ Ω
Day 4	2.1*10 ¹⁰ Ω	2.2*10 ¹⁰ Ω
Day 7	1.8*10 ¹⁰ Ω	1.9*10 ¹⁰ Ω

Standard Applications

SE-CURE™ 9650D is applied to the substrate by either a spray fluxing applicator or by jet dispensing. Flip chips are then placed onto the printed wiring substrates for the soldering operation.

Recommended Reflow Profile

Suggested reflow schedules are general guidelines for optimum properties of SE-CURE™ 9650D. SE-CURE™ 9650D is capable of being processed concurrently with normal surface mount components. Other reflow schedules are possible and may yield satisfactory results. Soldering occurs during a normal surface mount reflow process in nitrogen (< 700 ppm O₂).



Cleaning

SE-CURE™ 9650D is a no-clean formula. The ultra-low residues do not need to be removed for flip chip applications. Although SE-CURE™ 9650D is designed for no-clean applications, its residues can be easily removed using automated cleaning equipment (in-line or batch) with the aid of a solvent system (isopropanol, acetone, etc.). Equipment, mis-jetted or sprayed substrates, and rework sights can be cleaned using a solvent system (isopropanol, acetone, etc.).

Storage, Handling and Shelf Life

The recommended storage condition to maintain consistent viscosity, flux characteristics and overall performance is a temperature of 22 to 25 °C (72 to 77 °F). Shelf life is 12 months from date of manufacture when handled properly and held at 22 to 25 °C (72 to 77 °F).

Health and Safety

This product, during handling or use, may be hazardous to your health or the environment. Read the Safety Data Sheet and warning label before using this product. Safety Data Sheets are available at <https://www.kester.com/downloads/sds>.

Contact Information

To confirm this document is the most recent version, please contact Assembly@MacDermidAlpha.com

North America 800 West Thorndale Avenue Itasca, IL USA 60143 Phone: +1 800.2.KESTER	Asia Pacific 8/F., Paul Y. Centre 51 Hung To Road Kwun Tong, Kowloon, Hong Kong Phone: +852.3190.3100	Europe Ganghofer Strasse 45 82216 Gernlinden, Germany Phone: +49 (0) 8142 4785 0
---	--	--

Also read carefully warning and safety information on the Safety Data Sheet. This data sheet contains technical information required for safe and economical operation of this product. READ IT THOROUGHLY PRIOR TO PRODUCT USE. Emergency safety directory assistance: US 1 202 464 2554, Europe + 44 1235 239 670, Asia + 65 3158 1074, Brazil 0800 707 7022 and 0800 172 020, Mexico 01800 002 1400 and (55) 5559 1588

DISCLAIMER: All statements, technical information and recommendations contained herein are based on tests we believe to be reliable, but the accuracy or completeness thereof is not guaranteed. No statement or recommendation shall constitute a representation unless set forth in an agreement signed by officers of seller and manufacturer. NO WARRANTY OF MERCHANTABILITY, WARRANTY OF FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY IS MADE. The following warranty is made in lieu of such warranties and all other warranties, express, implied, or statutory. Products are warranted to be free from defects in material and workmanship at the time sold. The sole obligation of seller and manufacturer under this warranty shall be to replace any noncompliant product at the time sold. Under no circumstances shall manufacturer or seller be liable for any loss, damage or expense, direct, indirect, incidental or consequential, arising out of the inability to use the product. Notwithstanding the foregoing, if products are supplied in response to a customer request that specifies operating parameters beyond those stated above, or if products are used under conditions exceeding said parameters, the customer by acceptance or use thereof assumes all risk of product failure and of all direct, indirect, incidental and consequential damages that may result from use of the products under such conditions, and agrees to exonerate, indemnify, defend and hold harmless MacDermid, Incorporated and its affiliates therefrom. No suggestion for product use nor anything contained herein shall be construed as a recommendation to use any product in a manner that infringes any patent or other intellectual property rights, and seller and manufacturer assume no responsibility or liability for any such infringement.

© 2019 MacDermid, Inc. and its group of companies. All rights reserved. "®" and "™" are registered trademarks of MacDermid, Inc. and its group of companies in the United States and/or other countries.